

Truex 960 Handheld Portable X Ray Spectrometer Mineral Ore Gold Testing Machine

Basic Information

- Place of Origin:
- Brand Name:
- Certification:
- Minimum Order Quantity: 100
- Packaging Details: 付款方式

00

2

3

- Delivery Time: 供能力
- Payment Terms: 期限
- Supply Ability: 常包装



Product Specification

• Customized Support:

• Name:

Detector:Battery:

• Certification:

• Warranty:

• Thickness:

• Metal:

Brand Name:Power:

Handheld Mineral Xrf Analyzer OEM, OEM Zealchon Electronic BOOST Si-pin Detector1.6Kg(with Battery) Lithium Battery ISO 1 Year Type Iron 203*193*15cm

840~1300MW

Iron

Iron

- Box Type: Self Erecting Boxes
- Radiation Power:
- Metal Type:
- Metal Type:
- Universal Type: Fit For 80% Model Cars' Injectors



Our Product Introduction

Truex 960 Handheld Portable X Ray Spectrometer Mineral Ore Gold Testing Machine

Product description:

TrueX 960 Standard configuration mode analysis range, such as special elements, can be added Mg,Al,Si,P,S,Cl,K ,Ca,Ti,V,Cr,Mn,Fe,Co,Ni,Cu,Zn,As,Se,Rb,Sr,Y,Zr,Nb,Mo,Ag,Cd,Sn,Sb,Hf,Ta,W,Au,Hg,Pb,Bi.

Product specification:

| Weight | 1.6Kg(with battery). |
|------------------------|--|
| Dimensions | 254 x 79 x 280 mm(L x W x H). |
| Excitation | 50KV/200µA maximum pipe pressure pipe flow can be adjusted freely,Agtarget |
| source | (standard),Au,W,Rh target(optional). |
| Detector | BOOST Si-PIN detector |
| Range of detection | All elements between Mg and U. |
| Display system | Industrial resistive touch screen with screen size of 4.3". |
| | Proprietary operating system software and sound waves. |
| | Multiple languages including English and Chinese. |
| | And it automatically adjusts display brightness according to the environment brightness. |
| Data processing | 32GB memory USB, bluetooth, WIFI, or liked to the Internet; instrument can be configured and repaired remotely. Data can be exported via EXCEL or PDF. Users can customize the reports by adding their company logos, addresses, test results, spectrum and others (such as product description, origin and batch number). |
| Heat | Equipped with a dedicated T-shaped radiator to dissipate the heat no need to wait for |
| dissipation | cooling of detector time again. |
| Safety | Built-in double beam technology can automatically sense whether there is a sample at the measurement window. This is also a safety and protection feature. Waterproof, dust-proof and shockproof suitcase Drawell Safety Band |
| Power supply system | Intelligent battery management through MSBUS bus, real-time monitoring of the residual capacity of battery and backup battery. The battery complies with air transport regulations of dangerous goods. A single battery can last 8 hours. |

Application Features:

1. Excellent Performance

TrueX shows element symbols in both English and Chinese. With high precision, high testing speed and comparable results to even that of laboratory equipment, TrueX displays alloy grade and elements percentage content (up to three decimals) and ppm content in an apparent way. 2. One-touch operation TrueX test lasts only a few seconds and identification of alloy grades takes only 1 or 2 seconds. This facilitates operation by non-technical users.

3. Nondestructive testing (NDT) TrueX test does not damage or have any adverse effect on the use of samples. No damage is foreseen in the entire test process.

4. Zealchon analysis software

Zealchon analysis software is a professional analysis software which enables the users to easily configure passwords, customize analysis reports attached with company LOGO and implement remote control of machine; users can edit alloy grade library, add their own grade number or define their own company's alloy brands; the software also allows automatic calibration of instrument and diagnosis of probms in a remote way; the software can be updated via Internet.

Application fields: - Nondestructive, rapid and accurate analysis of alloy elements and alloy grade identification on the site - Metal identification /scrap metal sorting - QA/QC management in metal production, processing, casting, etc - Medicine and biological medicine - Identification of positive materials, oil refining and petrochemical industry - Thermal power plant, hydroelectric power station, nuclear power plant - Accurate element analysis of raw material and PMI identification so as to meet production needs and ensure security of equipment and materials used in the process.

FAQ:

- Q: Are you trade company or manufacturer?
- A: Fangji is a manufacturer who has more than 10 years experienced for security products.
- Q: Where is your company? Can I come to visit?
- A: We are in Shenzhen, China and welcome you to visit us anytime!
- Q: Do you ship worldwide?
- A: Yes, sure. we ship worldwide by air, by sea and by express etc.
- Q: Can you provide customized products?
- A: Yes, sure. Just provide your demands and requirements, then we will provide you the best items.

| Ellawig companys |
|--|
| +86-15399918960 Service@ellawigss.com ladyshairextensions.com |
| Room 501, unit 6, building 20, North Lane, east flower market, Beijing |